



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSD16168 16X16X8 N4/12 Gry HC, QTR TRN LTCH

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | CSD16168 |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Concept Single-Door Enclosure, 16.00X16.00X8.00, Gray, Steel |
| Weight per unit | 21.0 (lbs/each) |
| Product Category | Nema Types 4 & 12 Metallic Enc |

Features

| | |
|-----------|------------|
| ip rating | IP66 |
| Material | MILD STEEL |

Material, Color, and Finish

| | |
|------------|---------------|
| Color | Gray |
| Color Code | ANSI 61 |
| Finish | Powder Coated |

Dimensions and Weight

| | |
|--------|---------------------|
| Depth | 8 |
| Height | 16 |
| Size | 16.00x16.00x8.00 in |
| Width | 16 |

Descriptions

| | |
|------------------------|--|
| Description | 16X16X8 N4/12 GRY HC,QTR TRN LTCH |
| extra long description | NVENT HOF CSD16168 Enclosure 16.00x |
| Features | Concept Enclosures have streamlined styling, flush quarter-turn latches and an attractive, durable finish. |
| Long Description | Concept Single-Door Enclosure, 16.00x16.00x8.00, Gray, Steel |
| Product Type | Enclosure 16.00X16.00X8.00 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510773908 |
| Manufacturers Part Number | CSD16168 |
| UPC | 783510773908 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | STEEL JUNCTION BOXES |
| Type | Mild Steel Wall Mounted Industrial Enclosures |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 21 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---------------------------------|
| Application | Controls and Drives |
| nema rating | 12 Indoor, dust-resistant |