



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSD242010 24X20X10 N4/12 PNTD Steel HC, QTR TRN LTCH *Hoffman Enclosures, Inc.*

| | |
|------------------|---|
| Catalog Number | CSD242010 |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Concept Single-Door Enclosure, 24.00X20.00X10.00, Gray, Steel |
| Weight per unit | 36.0 (lbs/each) |
| Product Category | Nema Types 4 & 12 Metallic Enc |

Features

| | |
|-----------|-------|
| ip rating | IP66 |
| Material | Steel |

Material, Color, and Finish

| | |
|------------|---------------|
| Color | ANSI 61 GRAY |
| Color Code | ANSI 61 |
| Finish | Powder Coated |

Dimensions and Weight

| | |
|--------|----------------------|
| Depth | 10 |
| Height | 24 |
| Size | 24.00x20.00x10.00 in |
| Width | 20 |

Descriptions

| | |
|------------------------|--|
| Description | 24X20X10 N4/12 PNTD STEEL HC, QTR TRN LTCH |
| extra long description | NVENT HOF CSD242010 Wall-Mount Type |
| Features | Concept Enclosures have streamlined styling, flush quarter-turn latches and an attractive, durable finish. |
| Long Description | Concept Single-Door Enclosure, 24.00x20.00x10.00, Gray, Steel |
| Product Type | Wall-Mount Type 4, 12 Enclosure |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510374891 |
| Manufacturers Part Number | CSD242010 |
| UPC | 783510374891 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | STEEL JUNCTION BOXES |
| Type | Mild Steel Wall Mounted Industrial Enclosures |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 36 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Controls and Drives

nema rating

12 Indoor, dust-resistant