ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS220BK Switch Toggle DP 20A 120/277V Swire BK

Eaton Wiring Devices

Catalog Number	CS220BK
Manufacturer	Eaton Wiring Devices
Description	Eaton Commercial Grade Toggle Switch, #14-10 Awg, 20A, Commercial, Flush, 120/277V, Side Wire, Screw, Black, Load Type: Motor Control, Fan, Led, Incandescent, Elv, MLV, CFL, Flourescent, Halogen, Double-Pole, Dual-Pole, Brass, PVC
Weight per unit	0.1370 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	20
dimensions	1.3000 IN X 0.9020 IN X 4.2000 IN
Material	PVC
Poles	Two-pole
Voltage Rating	120/277 V

Descriptions

Description	SWITCH TOGGLE DP 20A 120/277V SWIRE BK
extra long description	EWD CS220BK Switch Toggle DP 20A 12
Features	Eaton's Arrow Hart commercial specification grade switches are designed to provide superior quality, reliability and performance in a variety of commercial environments.
Long Description	Eaton commercial grade toggle switch, #14-10 AWG, 20A, Commercial, Flush, 120/277V, Side wire, Screw, Black, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Double-Pole, Dual-pole, Brass, PVC
Product Type	Switch Toggle DP 20A 120/277V Swire BK
Special Features	Commercial Grade

Manufacturer Information

Brand	Eaton Wiring Devices
GTIN	00032664555923
Manufacturers Part Number	CS220BK
UPC	032664555923

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Commercial grade toggle switch

Packaging

Carton	10
Package	50
Weight Per each	0.137

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	cULus Listed,NOM,Federal Specification Classification 6241 05