



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSSL484000LMMV4 4' Led Strip 40K 4000LM Dim 80cri

Lithonia Lighting

Catalog Number	CSSL484000LMMV4
Manufacturer	Lithonia Lighting
Description	The Lithonia Lighting® CSS Strip Light With Adjustable Light Output and Switchable White Technology Is The Easiest Strip to Order, Stock, and Install, Perfect For Almost Any Basic Application. The Size and Versatility Make Them Suitable For Tight Spaces and For Task Lighting, Restrooms, Under/Over Cabinet and Storage Closets.
Weight per unit	5.0 (lbs/each)
Product Category	Lighting

Features

dimensions	48.00 x 2.62 x 2.3
Fixture Type	Strip Light
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	4000
Material	Steel
media	Yes
Shape	Rectangular
Voltage Rating	120-277
Wattage	35.3

Material, Color, and Finish

Color	White
color rendering index (cri)	80
color temperature	4000
Finish	Gloss

Dimensions and Weight

Height	2.25
Length	48
Size	48.00x2.62x2.22 IN
Width	2.625



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	New Construction
Description	4' LED STRIP 40K 4000LM DIM 80CRI
extra long description	LITH CSS L48 4000LM MVOLT 40K 80CRI
Features	Contractor Select
Long Description	The Lithonia Lighting® CSS strip light with Adjustable Light Output and Switchable White Technology is the easiest strip to order, stock, and install, perfect for almost any basic application. The size and versatility make them suitable for tight spaces and for task lighting, restrooms, under/over cabinet and storage closets.
Product Type	Strip Light

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193048852622
Manufacturers Part Number	CSS L48 4000LM MVOLT 40K 80CRI
UPC	193048852622

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Strip Light

Trade Size

aperture size	4FT
---------------	-----

Packaging

Carton	1
Weight Per each	5

Uses, Certifications, and Standards

Application	Education,Government,Hospitality,House of Worship,Offices & Banks,Residential,Retail,Sports and Recreation,Utility, Closet
environmental conditions	Indoor
Mounting	Surface,Suspended
standard	CSADLC Standard