



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy
30165-0000, GA Rome
Phone: 706-622-4953
Fax: 706-622-4954



CSB220V Switch Toggle DP 20A 120/277V B/Swire Iv *Eaton Wiring Devices*

Catalog Number	CSB220V
Manufacturer	Eaton Wiring Devices
Description	Eaton Commercial Grade Toggle Switch, #14-10 Awg, 20A, Commercial, Flush, 120/277V, Back and Side, Screw, Ivory, Load Type: Motor Control, Fan, Led, Incandescent, Elv, MLV, CFL, Flourescent, Halogen, Double-Pole, Dual-Pole, Brass, PVC
Weight per unit	0.1680 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	20
dimensions	1.3000 IN X 0.9020 IN X 4.2000 IN
Material	PVC
Poles	Two-pole
Voltage Rating	120/277 V

Descriptions

Description	SWITCH TOGGLE DP 20A 120/277V B/SWIRE IV
extra long description	EWD CSB220V Switch Toggle DP 20A 12
Features	Eaton's Arrow Hart commercial specification grade switches are designed to provide superior quality, reliability and performance in a variety of commercial environments.
Long Description	Eaton commercial grade toggle switch, #14-10 AWG, 20A, Commercial, Flush, 120/277V, Back and side, Screw, Ivory, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Double-Pole, Dual-pole, Brass, PVC
Product Type	Switch Toggle DP 20A 120/277V B/Swire Iv
Special Features	Commercial Grade

Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664559099
Manufacturers Part Number	CSB220V
UPC	032664559099

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Commercial grade toggle switch

Packaging

Carton	1
Package	50
Weight Per each	0.168



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy
30165-0000, GA Rome
Phone: 706-622-4953
Fax: 706-622-4954

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

cULus Listed,NOM