



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street
75482-0000, TX Sulphur Springs
Phone: 903-885-0024
Fax: 903-885-0352



CT106 4-5AWG Cu C-Tap

Nsi Industries

Catalog Number	CT106
Manufacturer	Nsi Industries
Description	Copper C Tap Grounding Connector For 3 to 4 Awg Copper "C" Taps Ensure Positive, All Around Compression With Low-Resistance and High Pull-Out Values. Made Of High Conductivity Copper, They Satisfy The Requirements Of NEC250-81 and 250-91 For Connecting to The Grounding Electrode System. Rated 600 Volts.
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Conductor Size	4 AWG
Material	Copper
Tap Size	4 AWG
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Pink
Finish	COPPER

Dimensions and Weight

Size	4-4 AWG
------	---------

Descriptions

Description	4-5AWG CU C-TAP
extra long description	NSI CT-106 C Tap Copper 3-4 Main
Features	Copper C Tap Grounding Connector for 3 to 4 AWG Copper "C" Taps ensure positive, all around compression with low-resistance and high pull-out values. Made of high conductivity copper, they satisfy the requirements of NEC250-81 and 250-91 for connecting to the grounding electrode system. Rated 600 Volts.
Long Description	Copper C Tap Grounding Connector for 3 to 4 AWG Copper "C" Taps ensure positive, all around compression with low-resistance and high pull-out values. Made of high conductivity copper, they satisfy the requirements of NEC250-81 and 250-91 for connecting to the grounding electrode system. Rated 600 Volts.
Product Type	C Tap Copper 3-4 Main
Special Features	4-4 AWG



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street
75482-0000, TX Sulphur Springs
Phone: 903-885-0024
Fax: 903-885-0352

Manufacturer Information

Brand	Polaris
GTIN	00662381098054
Manufacturers Part Number	CT-106
UPC	662381098054

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	C-Taps

Packaging

Carton	1
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486
Temperature Rating	90 C