ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# CTH24 8SOL-4STR Cu C Tap

*Nsi Industries*

| | |
|---|---|
| Catalog Number | CTH24 |
| Manufacturer | Nsi Industries |
| Description | Heavy Duty Copper C Tap For 2 Awg Applications: Copper "C" Taps Are Range-Taking Compression Connectors Made From High Conductivity Copper Alloy. Ideal For Making Tap or Parallel Copper Connections From 8 Sol to 4/0 STR Conductors. Provides Consistent Reliability With Heavy Wall Construction That Prevents Relaxation Of The Joint After Installation. Installation Time Is Reduced Because Of Its "C" Shape. Ul CU486A, 467 Suitable For Direct Burial and Csa Rated Electrical and Grounding. |
| Weight per unit | 0.0760 (lbs/each) |
| Product Category | Large Terminals & Connectors |

## Features

| | |
|---|---|
| Conductor Size | (Run) 2 SOL-2 STR |
| Material | Copper |
| Tap Size | 8 SOL-4 STR |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

## Material, Color, and Finish

| | |
|---|---|
| Color | Copper |
| Finish | COPPER |

## Dimensions and Weight

| | |
|---|---|
| Size | L=.750 - W=.625 - H=1.00 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Descriptions

| | |
|---|---|
| Description | 8SOL-4STR CU C TAP |
| extra long description | NSI CTH-24 C Tap Copper 2-2 Main 8- |
| Features | Heavy Duty Copper C Tap for 2 AWG APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial and CSA rated Electrical and Grounding. |
| Long Description | Heavy Duty Copper C Tap for 2 AWG APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial and CSA rated Electrical and Grounding. |
| Product Type | C Tap Copper 2-2 Main 8-4 Tap |
| Special Features | (Run) 2 SOL-2 STR - (Tap) 8 SOL-4 STR |

## Manufacturer Information

| | |
|---|---|
| Brand | Nsi Industries |
| GTIN | 00662381022165 |
| Manufacturers Part Number | CTH-24 |
| UPC | 662381022165 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | T&B C TAP LUGS |
| Type | Copper C Taps |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Weight Per each | 0.076 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Terminate-Splice-Tap |
| environmental conditions | 90 C |
| Temperature Rating | 90 C |