



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG132031FBC21C DG1 230V FR3 N1 10HP 31A CT 15HP 48A VT W/ BC Eaton Corp

Catalog Number	DG132031FBC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 208-240V Input 7.5 KW 10 HP CT 3PH 50/60 HZ 31A Output IP21/Type 1 FR3 LCD Internal Emc Filter and DC Choke Ethernet, RS-485, Bacnet MS/TP, Modbus TCP and Rtu Ports 2 Exp Slots Brake Chopper
Weight per unit	53.0 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	230 V, 208-240 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	27
Height	16
Width	12

Descriptions

Description	DG1 230V FR3 N1 10HP 31A CT 15HP 48A VT W/ BC
extra long description	ETN DG1-32031FB-C21C DG1,230V FR3,N
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 208-240V input 7.5 kW 10 Hp CT 3PH 50/60 Hz 31A output IP21/type 1 FR3 LCD Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU ports 2 exp slots Brake chopper
Product Type	DG1, 230V FR3, N1, 10HP, 31A/15HP, 48A, BC
Special Features	Coated board

Manufacturer Information

Brand	Eaton
GTIN	00786685886084
Manufacturers Part Number	DG1-32031FB-C21C
UPC	786685886084



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DRIVES

Type Variable Frequency Drive

Packaging

Carton 1

Weight Per each 53

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

Enclosure IP21/type 1 enclosure

standard UL 508C,EN 62061,cUL Listed,UL Listed,EN ISO 13849-1,IEC
61508,C-Tick Compliant,RoHS Compliant,CE Marked,GoST-R