



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH221NRK 30A/2P HD Fusible Safety Switch W/Neut 240V Nema3r

Eaton Corp

Catalog Number	DH221NRK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Fused Safety Switch, 30 A, Nema 3R, Painted Galvanized Steel, Class H, Fusible With Neutral, Two-Pole, Three-Wire, 240 V, Max HP: 1.5, 3 HP/3, 7.5 HP/5 HP (1, 3PH @ STD Fuse/Time Delay/250 VDC)
Weight per unit	19.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	30
dimensions	16.5000 IN X 9.1200 IN X 8.3100 IN
Material	Galvanized Steel
media	Yes
Poles	2
Voltage Rating	240V

### Dimensions and Weight

Depth	16.5000
Height	8.3100
Width	9.1200

### Descriptions

Description	30A/2P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA3R
extra long description	ETN DH221NRK 30A/2P HD FSBL Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton enhanced visible blade single-throw fused safety switch, 30 A, NEMA 3R, Painted galvanized steel, Class H, Fusible with neutral, Two-pole, Three-wire, 240 V, Max Hp: 1.5, 3 hp/3, 7.5 hp/5 hp (1,3PH @ Std fuse/time delay/250 Vdc)
Product Type	30A/2P HD FSBL Sfty SW W/Neut 240V N3R

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113205359
Manufacturers Part Number	DH221NRK
UPC	782113205359



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... DISCONNECTS

Type ..... Fusible safety switch

## Packaging

Carton ..... 1

Weight Per each ..... 19

## Uses, Certifications, and Standards

Application ..... Commercial / Institutional Buildings / Structures - Power  
Distribution and Controls

nema rating ..... 3R

standard ..... UL Listed, CSA Certified