



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH321FRK 30A/3P HD Fusible Safety Switch 240V Nema 3R

Eaton Corp

Catalog Number	DH321FRK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Safety Switch, 30 A, Nema 3R, Painted Galvanized Steel, Class H, Fusible Without Neutral, Three-Pole, Three-Wire, 240 V, Max HP: 1.5, 3/ 3, 7.5/ 5 HP (1, 3PH @STD/TD, 250 VDC), #14-#2 Cu/Al
Weight per unit	19.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	30
Material	Painted galvanized steel
media	Yes
Poles	3
Voltage Rating	240V

### Dimensions and Weight

Depth	16.5
Height	16.27
Width	9.5

### Descriptions

Description	30A/3P HD FUSIBLE SAFETY SWITCH 240V NEMA 3R
extra long description	ETN DH321FRK 30A/3P HD FUSIBLE Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Enhanced visible blade single-throw safety switch, 30 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Three-pole, Three-wire, 240 V, Max Hp: 1.5, 3/ 3, 7.5/ 5 hp (1,3PH @Std/TD, 250 Vdc), #14-#2 Cu/Al
Product Type	30A/3P HD Fusible Sfty SW 240V N3R

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113208497
Manufacturers Part Number	DH321FRK
UPC	782113208497



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... DISCONNECTS

Type ..... Fusible safety switch

## Packaging

Carton ..... 1

Weight Per each ..... 19

## Uses, Certifications, and Standards

Application ..... Commercial / Institutional Buildings / Structures - Power  
Distribution and Controls

nema rating ..... 3R

standard ..... UL Listed