



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH326NRK 600A/3P HD Fusible Safety Switch W/Neut 240V Nema

Eaton Corp

Catalog Number	DH326NRK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 600 A, Nema 3R, Painted Galvanized Steel, Class H, Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 75, 200 HP (3PH @STD, TD)), (1)#2-(1)600 Kcmil and (1)#1/0-(1)750 Kcmil Al
Weight per unit	155.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	600
dimensions	12.8400 IN X 23.6600 IN X 51.8300 IN
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	240V

### Dimensions and Weight

Depth	12.8400
Height	51.8300
Width	23.6600

### Descriptions

Description	600A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA
extra long description	ETN DH326NRK 600A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 600 A, NEMA 3R, Painted galvanized steel, Class H, Neutral, Three-pole, Four-wire, 240 V, Max Hp: 75, 200 hp (3PH @Std, TD)), (1)#2-(1)600 kcmil and (1)#1/0-(1)750 kcmil Al
Product Type	600A/3P HD FSBL Sfty SW W/Neut 240V N3R

### Manufacturer Information

Brand	Eaton
GTIN	00782113207421
Manufacturers Part Number	DH326NRK
UPC	782113207421



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

## Packaging

Carton 1

Weight Per each 155

## Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power  
Distribution and Controls

nema rating 3R

standard UL Listed, NEC 230.62 (C) Compliant Barrier