



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH363NGK 100A/3P HD Fusible Safety Switch 600V W/Neut Nema1

Eaton Corp

Catalog Number	DH363NGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 100 A, Nema 1, Painted Steel, Class H, Fusible With Neutral, Three-Pole, Four-Wire, 600 V, Max HP: 30, 40/ 60, 75 HP (1/3PH @480, 600 V), #14-#1/0 Cu/Al
Weight per unit	23.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	100
dimensions	22.5000 IN X 12.7500 IN X 9.0000 IN
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	600 V

### Dimensions and Weight

Depth	22.5
Height	9
Width	12.75

### Descriptions

Description	100A/3P HD FUSIBLE SAFETY SWITCH 600V W/NEUT NEMA1
extra long description	ETN DH363NGK 100A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 100 A, NEMA 1, Painted steel, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 30, 40/ 60, 75 hp (1/3PH @480, 600 V), #14-#1/0 Cu/Al
Product Type	100A/3P HD FSBL Sfty SW 600V W/Neut N1

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206486
Manufacturers Part Number	DH363NGK
UPC	782113206486



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... DISCONNECTS

Type ..... Fusible safety switch

## Packaging

Carton ..... 1

Weight Per each ..... 23

## Uses, Certifications, and Standards

Application ..... Commercial / Institutional Buildings / Structures - Power  
Distribution and Controls

nema rating ..... 1

standard ..... UL Listed, NEC 230.62 (C) Compliant Barrier