



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH365FGK 400A/3P HD Fusible Safety Switch 600V Nema 1

Eaton Corp

Catalog Number	DH365FGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 400 A, Nema 1, Painted Steel, Class H, Fusible Without Neutral, Three-Pole, Three-Wire, 600 V, Max HP: 250, 350 HP (3PH @480/600 V), (2)#1/0-(2)300 Kcmil; or (1)#1/0-(1)750 Kcmil Al
Weight per unit	105.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	400
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	600 V

### Dimensions and Weight

Depth	45.5
Height	10.25
Width	24.38

### Descriptions

Description	400A/3P HD FUSIBLE SAFETY SWITCH 600V NEMA 1
extra long description	ETN DH365FGK 400A/3P HD Fusible Sft
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 400 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 250, 350 hp (3PH @480/600 V), (2)#1/0-(2)300 kcmil; or (1)#1/0-(1)750 kcmil Al
Product Type	400A/3P HD Fusible Sfty SW 600V N1

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113207209
Manufacturers Part Number	DH365FGK
UPC	782113207209

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	105

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	1
standard	UL Listed, NEC 230.62 (C) Compliant Barrier