



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH366URK 600A/3P HD NF Safety Switch 600V Nema 3R

*Eaton Corp*

Catalog Number	DH366URK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 600 A, Nema 3R, Painted Galvanized Steel, Non-Fusible, Three-Pole, Three-Wire, 200 At 240 Vac TD 3 PH, 400 At 480 Vac TD 3 PH, 500 At 600 Vac TD 3 PH
Weight per unit	135.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

### Features

amperage rating	600
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	600 V

### Dimensions and Weight

Depth	14.07
Height	51.82
Width	25.01

### Descriptions

Description	600A/3P HD NF SAFETY SWITCH 600V NEMA 3R
extra long description	ETN DH366URK 600A/3P HD NF Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 600 A, NEMA 3R, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 200 at 240 Vac TD 3 Ph, 400 at 480 Vac TD 3 Ph, 500 at 600 Vac TD 3 Ph
Product Type	600A/3P HD NF Sfty SW 600V N3R

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113207582
Manufacturers Part Number	DH366URK
UPC	782113207582

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	135

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed, NEC 230.62 (C) Compliant Barrier