



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DG134205FNC21C DG1 480V FR6 N1 150HP 205A CT 200HP 261A VT Eaton Corp

Catalog Number	DG134205FNC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 380-500V Input 110 KW 150 HP CT 3PH 50/60 HZ 205A Output IP21/Type 1 Enclosure FR6 LCD Internal Emc Filter and DC Choke Ethernet, RS-485, Bacnet MS/TP, Modbus TCP and Rtu Ports 2 Exp Slots
Weight per unit	270.0 (lbs/each)
Product Category	Ac Drives

### Features

display	LCD graphical
Input Voltage	400 V, 380-500 V(-15%, +10%)
keypad	Included

### Dimensions and Weight

Depth	45
Height	16
Width	23

### Descriptions

Description	DG1 480V FR6 N1 150HP 205A CT 200HP 261A VT
extra long description	ETN DG1-34205FN-C21C POWERXL DG1 AF
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 380-500V input 110 kW 150 Hp CT 3PH 50/60 Hz 205A output IP21/type 1 enclosure FR6 LCD Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU ports 2 exp slots
Product Type	Powerxl DG1 Af Drive, 380-500V Input 110

### Manufacturer Information

Brand	Eaton
GTIN	00786680199752
Manufacturers Part Number	DG1-34205FN-C21C
UPC	786680199752

### Taxonomies, Classifications, and Categories

Type	Variable Frequency Drive
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	270

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL Listed,UL 508C,EN ISO 13849-1,cUL Listed,IEC 61508,EN 62061,RoHS Compliant,CE Marked,C-Tick Compliant,GoST-R