



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH323NGK 100A/3P HD Fusible Safety Switch W/Neut 240V Nema1

Eaton Corp

Catalog Number	DH323NGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 100 A, Nema 1, Painted Steel, Class H, Fusible, Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 7.5, 15/ 15, 30/ 20 HP (1, 3PH @STD/TD/250 VDC), #14-#1/0 Cu/Al
Weight per unit	23.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	100
dimensions	22.5000 IN X 12.7500 IN X 9.0000 IN
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	240V

Dimensions and Weight

Depth	22.5
Height	9
Width	12.75

Descriptions

Description	100A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA1
extra long description	ETN DH323NGK 100A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 100 A, NEMA 1, Painted steel, Class H, Fusible, Neutral, Three-pole, Four-wire, 240 V, Max Hp: 7.5, 15/ 15, 30/ 20 hp (1,3PH @Std/TD/250 Vdc), #14-#1/0 Cu/Al
Product Type	100A/3P HD FSBL Sfty SW W/Neut 240V N1

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206264
Manufacturers Part Number	DH323NGK
UPC	782113206264



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

Packaging

Carton 1

Weight Per each 23

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 1

standard UL Listed, NEC 230.62 (C) Compliant Barrier