



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH328NRK 1200A/3P HD Fusible Safety Switch 240V W/Neut Nema *Eaton Corp*

Catalog Number	DH328NRK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Safety Switch, 1200 A, Nema 3R, Painted Galvanized Steel, Class L, Fusible With Neutral, Three-Pole, Four-Wire, 240 V, (4)#1/0-(4)750 Kcmil Al
Weight per unit	465.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	1200
dimensions	72.0000 IN X 48.0000 IN X 21.0000 IN
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	240V

Dimensions and Weight

Depth	72
Height	21
Width	48

Descriptions

Description	1200A/3P HD FUSIBLE SAFETY SWITCH 240V W/NEUT NEMA
extra long description	ETN DH328NRK 1200A/3P HD FSBL Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Enhanced visible blade single-throw safety switch, 1200 A, NEMA 3R, Painted galvanized steel, Class L, Fusible with neutral, Three-pole, Four-wire, 240 V, (4)#1/0-(4)750 kcmil Al
Product Type	1200A/3P HD FSBL Sfty SW 240V W/Neut N3R

Manufacturer Information

Brand	Eaton
GTIN	00782114313008
Manufacturers Part Number	DH328NRK
UPC	782114313008

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	465

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed