



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH363FDK 100A/3P HD Fusible Safety Switch 600V Nema 12

Eaton Corp

Catalog Number	DH363FDK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Receptacle Safety Switch, 100 A, Nema 12/3R, Painted Galvanized Steel, Class H, Fusible Without Neutral, Three-Pole, Three-Wire, 600 V, Max HP: 30, 40/ 60, 75 HP (1/3PH @480, 600 V), #14-#1/0 Cu/Al
Weight per unit	29.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	100
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	600 V

### Dimensions and Weight

Depth	25.5
Height	9
Width	13.25

### Descriptions

Description	100A/3P HD FUSIBLE SAFETY SWITCH 600V NEMA 12
extra long description	ETN DH363FDK 100A/3P HD Fusible Sft
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty receptacle safety switch, 100 A, NEMA 12/3R, Painted galvanized steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 30, 40/ 60, 75 hp (1/3PH @480, 600 V), #14-#1/0 Cu/Al
Product Type	100A/3P HD Fusible Sfty SW 600V N12

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206554
Manufacturers Part Number	DH363FDK
UPC	782113206554



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... DISCONNECTS

Type ..... Fusible safety switch

## Packaging

Carton ..... 1

Weight Per each ..... 29

## Uses, Certifications, and Standards

Application ..... Commercial / Institutional Buildings / Structures - Power  
Distribution and Controls

nema rating ..... 12;3R

standard ..... UL Listed