



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DR10250L Disconnect *Panduit Corporation*

| | |
|------------------|---|
| Catalog Number | DR10250L |
| Manufacturer | Panduit Corporation |
| Description | The Vibration Resistant Female Disconnect Is Made Of Brass and Is Tin-Plated. It Is Non-Insulated In Metallic Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 12-10 Awg (4.0-6.0 MM ²). It Is 0.61" (15.5 MM) Long and 0.3" (7.6 MM) Wide. The Disconnect Has A Standard Barrel Configuration and A Sleeved Barrel. It Comes In Bottles Of 50. |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|----------|
| connection | Standard |
| insulation | None |
| Material | Brass |
| Voltage Rating | 600 |
| Wire Size | 10 |

Material, Color, and Finish

| | |
|--------|--------|
| Finish | Tinned |
|--------|--------|

Descriptions

| | |
|------------------------|---|
| Description | DISCONNECT |
| extra long description | PAN DR10-250-L Pan-Term® DR10-250-L |
| Long Description | The vibration resistant female disconnect is made of brass and is tin-plated. It is non-insulated in metallic housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 12-10 AWG (4.0-6.0 mm ²). It is 0.61" (15.5 mm) long and 0.3" (7.6 mm) wide. The disconnect has a standard barrel configuration and a sleeved barrel. It comes in bottles of 50. |
| Product Type | Pan-Term® DR10-250-L Loose Piece Disconnect |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983827367 |
| Manufacturers Part Number | DR10-250-L |
| UPC | 074983827367 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------|
| Category Description | TERMINALS |
| Type | Disconnect |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|----|
| Carton | 50 |
| Weight Per each | 1 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Mounting | 1932-09-01 |
| standard | CSA Certified LR31212, C22.2 No.153;UL 310 Listed, UL Listed 20H3 E78522 |
| Temperature Rating | 302 Degrees Fahrenheit (150 Degrees Celsius) |