



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVFSQLFWH Diva 1.5A/120W Fan/LT SP White *Lutron*

Catalog Number	DVFSQLFWH
Manufacturer	Lutron
Description	Lutron Diva 3-Speed Fan Control and Light Switch, Single-Pole/3-Way, 1.5A Fan/1A Led, White
Weight per unit	0.1300 (lbs/each)
Product Category	Fan Speed Switches & Controls

Features

actuator	Rocker switch
amperage rating	1.5 A fan
connection	Wire Leads
Contact Configuration	N-O
Contact Rating	1.5
media	Yes
Poles	1
Voltage Rating	120
Wattage	120/240 W light

Dimensions and Weight

Size	4.69 x 2.94
------	-------------

Descriptions

Description	DIVA 1.5A/120W FAN/LT SP WHITE
extra long description	LUT DVFSQ-LF-WH DIVA 3-SPEED LIGHT
Features	The Lutron Diva Light and Fan Switch helps you achieve the ideal comfort level for any home. It features an intuitive rocker switch to turn your lights on/off and a discreet 3-speed slider to increase or decrease the fan speed. This Diva Light/Fan Switch works with all LED, CFL, Incandescent, and Halogen bulbs. For use in single-pole applications with single ceiling paddle fans only. Coordinating Claro wall plate sold separately. Available in 20+ colors to consistently match any Lutron device.
Long Description	Lutron Diva 3-Speed Fan Control and Light Switch, Single-Pole/3-Way, 1.5A Fan/1A LED, White
Product Type	Diva 3-Speed Light Switch In White
Special Features	Fan control (top) Slide up to on/increase speed, down to decrease/off. 3 quiet fan speeds designed to prevent motor hum (for use with only one ceiling paddle fan). Switch (bottom) Rocker switch turns light on/off.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00784276226677
Manufacturers Part Number	DVFSQ-LF-WH
UPC	784276226677

Taxonomies, Classifications, and Categories

Category Description	CEILING FANS AND ACCESSORIES
Type	Fan/light control, 3-way/single-pole

Packaging

Carton	1
Weight Per each	0.13

Uses, Certifications, and Standards

Application	Lighting and Fan Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL, NOM