



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E10168354 #2-2/0 GRN DBL Set Screw ML Plug *Crouse-Hinds*

Catalog Number	E10168354
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Cam-Lok J Series E1016 Plug, Up to 300A Continuous, #2-2/0 Awg, Green, Double Set Screw, Brass Contacts, Male, Thermoplastic Elastomer (Tpe), Non-Vulcanized, 600 Vac/DC
Weight per unit	1.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	300
connection	Double Set Screw
dimensions	7.1800 IN X 1.5000 IN X 1.5000 IN
Poles	1
Voltage Rating	600 VAC/VDC
Wire Size	2 To 2/0 AWG

Dimensions and Weight

Size	1.50 In Diameter X 7.18 In Length
------	-----------------------------------

Descriptions

Description	#2-2/0 GRN DBL SET SCREW ML PLUG
extra long description	CRS-H E1016-8354 E1016 M P NV DSS N
Features	The Cam-Lok J series from Eaton's Crouse-Hinds Division provides the means to quickly connect and disconnect power systems safely. Cam-Lok is the industry standard for motors, generators, indoor and outdoor lighting distribution panels, and numerous other power applications.
Long Description	Eaton Crouse-Hinds series Cam-Lok J Series E1016 plug, Up to 300A continuous, #2-2/0 AWG, Green, Double set screw, Brass contacts, Male, Thermoplastic elastomer (TPE), Non-vulcanized, 600 Vac/dc
Product Type	E1016 M P NV DSS No 2 to 2/0 GR
Special Features	NEMA 3R Enclosure

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662275131591
Manufacturers Part Number	E1016-8354
UPC	662275131591



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	PLUG

Packaging

Carton	1
Package	10
Weight Per each	1

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	-40 To 105 Deg C
standard	UL, CSA