



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E57MAL18A2B1 18MM STD Ind Prox 2W Ac Mini Conn

Eaton Corp

Catalog Number	E57MAL18A2B1
Manufacturer	Eaton Corp
Description	Inductive Proximity Sensor, E57, Straight, Shielded, 360° Viewable Led, Mini, 250 Ma At 250V, 3 Pin, <3% Sensing Range, PVC, 2-Wire Ac, No, 20-250V
Weight per unit	0.3000 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

Accuracy	< 3% sensing range
connection	Mini
dimensions	3.3900 IN X 0.7100 IN X 0.7100 IN
media	Yes

Descriptions

Description	18MM STD IND PROX 2W AC MINI CONN
extra long description	ETN E57MAL18A2B1 18MM STD IND PROX
Features	E57G general purpose sensors are a cost-effective solution that is optimised to include only those functions that are necessary for basic, reliable sensing without lacking the performance or features you expect in an Eaton product. These sensors include various diameter options designed to fit a variety of applications.
Long Description	Inductive Proximity Sensor, E57, Straight, Shielded, 360° viewable LED, Mini, 250 mA at 250V, 3 pin, <3% sensing range, PVC, 2-wire AC, NO, 20-250V
Product Type	18MM STD Ind Prox 2W Ac Mini Conn

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113317748
Manufacturers Part Number	E57MAL18A2B1
UPC	782113317748

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Inductive Proximity Sensor

Packaging

Carton	1
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
environmental conditions	NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67, IP69K
standard	UL Listed, CSA Certified, CE Marked