



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E50DS3 E50 Heavy Duty Limit Switch

*Eaton Corp*

Catalog Number	E50DS3
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Head, Side Push Roller, Spring Ret, 14-250F(-10-121C), Screw Term, Nema 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, Diec ZN, UI, Csa, Ce
Weight per unit	0.1100 (lbs/each)
Product Category	Limit Switch Heads

### Features

dimensions	1.0500 IN X 1.5400 IN X 2.9400 IN
Material	Die Cast Zinc

### Dimensions and Weight

Depth	1.54
Height	2.94
Width	1.54

### Descriptions

Description	E50 HEAVY DUTY LIMIT SWITCH
extra long description	ETN E50DS3 E50 LS HEAD,SIDE PUSH RO
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Head,Side Push Roller,Spring Ret,14-250F(-10-121C),Screw term,NEMA 1,3,3S,4,4X,6,6P,13,IP67,Diec Zn,UL,CSA,CE
Product Type	E50 LS Head, Side Push Roller, Spring RTN

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113290645
Manufacturers Part Number	E50DS3
UPC	782113290645

### Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.11

## Uses, Certifications, and Standards

Application	Water and Wastewater Systems - Water and Wastewater Systems - Other Stationary Mach Equip In Factory - Machine Tools: Cutting Stationary Mach Equip In Factory - Machine Tools: Forming Ind Facilities & Factories - Industrial Facilities/Factories - Other
Operating Temperature standard	14 UL Recognized, CSA Certified, UL Listed, RoHS Compliant, CE Marked