

Eaton EABC26

Catalog Number: EABC26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover	EABC26
	UPC
	782274247809
Product Length/Depth	Product Height
5.56 in	3.75 in
Product Width	Product Weight
2.78 in	4 lb

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

Material

Feraloy iron alloy

NEMA Rating

3

4

7

9

Cover opening diameter

3"

Trade size

3/4"

Shape

C

Catalogs

Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page

Certification reports

Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification (EAB)

Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification (EAB)

Installation instructions

IF 1472 - EAB Condulet Conduit Outlet Bodies

IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes

Specifications and datasheets

Eaton Specification Sheet - EABC26

Technical service bulletins

Industrial Fittings Bend Radius and Cubic Capacity Chart

Eaton EABC26

Catalog Number: EABC26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover	EABC26
	UPC
	782274247809
Product Length/Depth	Product Height
5.56 in	3.75 in
Product Width	Product Weight
2.78 in	4 lb

[Area classification](#)

Hazardous/Classified Locations

[Standards type](#)

NEC/CEC

[NEC hazardous rating](#)

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

[Material](#)

Feraloy iron alloy

[NEMA Rating](#)

3

4

7

9

[Cover opening diameter](#)

3"

[Trade size](#)

3/4"

[Shape](#)

C

[Catalogs](#)

Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page

[Certification reports](#)

Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification (EAB)

Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification (EAB)

[Installation instructions](#)

IF 1472 - EAB Condulet Conduit Outlet Bodies

IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes

[Specifications and datasheets](#)

Eaton Specification Sheet - EABC26

[Technical service bulletins](#)

Industrial Fittings Bend Radius and Cubic Capacity Chart