



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ECN5412CACP6R63C Pump Panel - 30A Fusible SW Nema 3R SZ 1 480VAC CO *Eaton Corp*

Catalog Number	ECN5412CACP6R63C
Manufacturer	Eaton Corp
Description	Eaton Freedom Industrial Pump Panel, Fusible Disconnect, Nema 3R Painted Steel Enclosure, 460V/60 HZ, 440V/50 HZ Coil, 30A/600V Type R Fuse Clip, 4-20A Solid-State Electronic Overload Relay, Nema Size 1 Frame, Pushbutton Omitted
Weight per unit	75.0 (lbs/each)
Product Category	Reversing Starters With Circui

Features

Coil Voltage	460V/60 Hz, 440V/50 Hz
--------------	------------------------

Dimensions and Weight

Depth	40
Height	12
Width	20

Descriptions

Description	PUMP PANEL - 30A FUSIBLE SW NEMA 3R SZ 1 480VAC CO
extra long description	ETN ECN5412CAC-P6R63/C PP 30A FUS S
Features	Eaton's industrial pump panels are combination starters that are designed for irrigation, oil well, gas and other pump applications. The enclosure is NEMA Type 3R to provide weather-tight protection and is available in several sizes, depending on the customer's control option requirements. The disconnect, contactor and overload relay are the same as used in Freedom lines of combination starters.
Long Description	Eaton Freedom Industrial Pump Panel, Fusible disconnect, NEMA 3R Painted steel enclosure, 460V/60 Hz, 440V/50 Hz coil, 30A/600V Type R fuse clip, 4-20A solid-state electronic overload relay, NEMA size 1 frame, Pushbutton omitted
Product Type	PP 30A Fus SW N3R SZ1 480V CL

Manufacturer Information

Brand	Eaton
GTIN	00786685455259
Manufacturers Part Number	ECN5412CAC-P6R63/C
UPC	786685455259

Taxonomies, Classifications, and Categories

Category Description	PUMP PANELS
----------------------	-------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	75

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - OtherStationary Machinery and Equipment Outside Factory - Pumps and Compressors
standard	UL Listed,ABS Certified,cUL Listed,OSHPD Certified