



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ECN0531AAAR63E Non-Combo Nema 1 FVNR SZ 3 120VAC Coil

Eaton Corp

Catalog Number	ECN0531AAAR63E
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Motor Control Starter, 110V/50 HZ-120V/60 HZ, Nema 1, Non-Combination Non-Reversing Starter, Nema Size 3, 20-100A Solid-State Relay Without Ground Fault
Weight per unit	32.0 (lbs/each)
Product Category	Nema Non-Combination Starters

### Features

Coil Voltage	110V/50 Hz-120V/60 Hz
--------------	-----------------------

### Dimensions and Weight

Depth	26.5
Height	11
Size	NEMA size 3
Width	14.2

### Descriptions

Description	NON-COMBO NEMA 1 FVNR SZ 3 120VAC COIL
extra long description	ETN ECN0531AAA-R63/E NON-COMBO NEMA
Features	Eaton's Freedom starters and contactors feature a compact, space-saving design, using state-of-the-art technology and the latest in high strength, impact and temperature resistant insulating materials. In addition to the bimetallic overload, Eaton also offers a series of electronic overload relay (C440) available as a standalone unit and assembled with Freedom contactor.
Long Description	Eaton Freedom NEMA motor control starter, 110V/50 Hz-120V/60 Hz, NEMA 1, Non-combination non-reversing starter, NEMA size 3, 20-100A solid-state relay without ground fault
Product Type	Non-Combo Nema 1 FVNR SZ 3 120VAC Coil

### Manufacturer Information

Brand	Eaton
GTIN	00786685450995
Manufacturers Part Number	ECN0531AAA-R63/E
UPC	786685450995

### Taxonomies, Classifications, and Categories

Category Description	ENCLOSED
----------------------	----------

### Packaging

Carton	1
Weight Per each	32



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application	Unknown - Unknown: Undefined
standard	UL Listed file E1491,Contact Manufacturer