

Eaton ECN5552CAK

Catalog Number: ECN5552CAK

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, NEMA 3R painted steel enclosure, 440V/50 Hz-460V/60 Hz coil, NEMA size 5, 400A breaker



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Industrial pump panel	ECN5552CAK
UPC	Product Length/Depth
782114139165	66 in
Product Height	Product Width
23.5 in	42.5 in
Product Weight	Warranty
66.5 lb	1 year
Certifications	
cUL Listed	
UL Listed	
OSHDPD Certified	

defaultTaxonomyAttributeLabel

Coil voltage

440V/50 Hz-460V/60 Hz

Enclosure

NEMA 3R

Enclosure material

Painted steel

Type

Circuit breaker disconnect

Circuit breaker rating

400A

Size

NEMA size 5

Resources

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECN5552CAK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton ECN5552CAK

Catalog Number: ECN5552CAK

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, NEMA 3R painted steel enclosure, 440V/50 Hz-460V/60 Hz coil, NEMA size 5, 400A breaker



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Industrial pump panel	ECN5552CAK
UPC	Product Length/Depth
782114139165	66 in
Product Height	Product Width
23.5 in	42.5 in
Product Weight	Warranty
66.5 lb	1 year
Certifications	
cUL Listed	
UL Listed	
OSHDPD Certified	

defaultTaxonomyAttributeLabel

Coil voltage

440V/50 Hz-460V/60 Hz

Enclosure

NEMA 3R

Enclosure material

Painted steel

Type

Circuit breaker disconnect

Circuit breaker rating

400A

Size

NEMA size 5

Resources

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECN5552CAK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)