



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ELL4G Ocal 4", 90D 40MIL PVC CTD HDG Rigid Elbow

*Abb Installation Products, Inc*

Catalog Number	ELL4G
Manufacturer	Abb Installation Products, Inc
Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 4 Inch/103 Metric, Angle 90 Degrees, Radius 16 Inch/406.40 Millimeters, Offset 21-3/4 Inch/552.45 Millimeters, Straight End 5-3/4 Inch/146.05 Millimeters, Unbent Length 36.63 Inch/930.47 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Weight per unit	33.1 (lbs/each)
Product Category	Steel

### Material, Color, and Finish

Color	Gray
Finish	Hot Dip Galvanized

### Dimensions and Weight

Depth	36.63
-------	-------

### Descriptions

Description	OCAL 4", 90D 40MIL PVC CTD HDG RIGID ELBOW
extra long description	ABB ELL4-G PVC CTD ELBOW 90D 4IN ST
Long Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 4 Inch/103 Metric, Angle 90 Degrees, Radius 16 Inch/406.40 Millimeters, Offset 21-3/4 Inch/552.45 Millimeters, Straight End 5-3/4 Inch/146.05 Millimeters, Unbent Length 36.63 Inch/930.47 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Product Type	PVC CTD Elbow 90D 4IN Steel Gray
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size

### Manufacturer Information

Brand	OCAL
GTIN	00704508370688
Manufacturers Part Number	ELL4-G
UPC	704508370688

### Taxonomies, Classifications, and Categories

Category Description	Plastibond, Fiberglass Conduit & Fittings
Type	Conduit Elbow - Standard Radius

### Trade Size

Trade Size	4 in , 103 mm
------------	---------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	33.12

## Uses, Certifications, and Standards

Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
standard	cULus E46453, CSA