



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EGE3020FFG E 3P 20A 25KA Fixed Thermal Fixed Mag Single Pack

*Eaton Corp*

Catalog Number	EGE3020FFG
Manufacturer	Eaton Corp
Description	Eaton Series G Complete Molded Case Circuit Breaker. 3P 20A 25KA, Fixed, Thermo Magnetic, Single Pack
Weight per unit	2.8 (lbs/each)
Product Category	3 Pole Interchangeable Trip TH

### Features

Current Rating	20 A
dimensions	2.9902 IN X 3.0000 IN X 5.5000 IN
frame	EG
media	Yes
Poles	Three-pole
Voltage Rating	600Y/347 Vac

### Descriptions

Description	E 3P 20A 25KA FIXED THERMAL FIXED MAG SINGLE PACK
extra long description	ETN EGE3020FFG E 3P 20A 25KA FIXED
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G complete molded case circuit breaker. 3P 20A 25kA, fixed, thermo magnetic, single pack
Product Type	E 3P 20A 25KA Fixed TM Single PK CB

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116131389
Manufacturers Part Number	EGE3020FFG
UPC	782116131389

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	2.7799

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	IEC Rated,UL Listed,CSA Certified,CE Marked,RoHS conform