

**NEW!**  
more on  
reverse

# Non-Metallic Insulating Bushings for EMT

*Cable Protection at its Best*



**Easy installation on EMT!**



**NEW!**

Arlington's non-metallic Insulating Bushings protect cable from abrasion when using EMT, Rigid, IMC or PVC rigid conduit – holding firmly in place as cable is pulled through.

When used for cable protection only these insulating bushings are a perfect substitution for costly fittings. Uses include power, computer data lines, cable TV, audio/video cables, phone, or alarm/security systems.

**Try our new, convenient SPLIT bushings. They're perfect for easy installation on EMT, and other conduit when cables are already in place.**

**SPLIT bushings are available in 2", 2-1/2", 3", 3-1/2" and 4" trade sizes. Look for the 'S' suffix in the chart on reverse.**

Arlington Insulating Bushings...

- Listed for use in environmental air handling spaces per 2014 NEC requirements 300-22(c)
- Meet 2014 NEC requirements for 300-15(c) protection
- UL/CSA Listed



Scan for info



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517

**800/233.4717**


**Fax 570/562.0646**

**www.aifittings.com**

**EMT400S**  
4" Split Insulating Bushing  
\*Cable tie included


# Insulating Bushings for EMT, Rigid, IMC, PVC

Listed for Environmental Air Handling Spaces



**Fast, easy installation**  
 Press fit onto EMT.  
 Place board over bushing and tap onto conduit for extra-firm hold.

Arlington's Insulating Bushings meet 2014 NEC requirements for 300-15(c) protection



**EMT50**  
 1/2" Insulating Bushing for EMT

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	Trade Size	DESCRIPTION Insulating Bushings	UNIT PKG	STD PKG
EMT50	12200	1/2"	Press-fit	100	1000
EMT75	12205	3/4"		100	1000
EMT100	12220	1"	Non-metallic	100	100
EMT125	12225	1-1/4"	Insulating Bushings for use with EMT	100	100
EMT150	12230	1-1/2"		100	100
EMT200	12235	2"	Insulating Bushing wv Split	50	50
EMT200S	15301	2"		50	50

**These larger EMT Bushings can also be used with rigid, IMC, PVC conduit**

EMT250	12240	2-1/2"		25	25
EMT300	12245	3"		25	25
EMT350	12250	3-1/2"		25	25
EMT400	12255	4"		25	25
EMT250S	12270	2-1/2"	Insulating Bushing wv Split	25	25
EMT300S	12271	3"	Insulating Bushing wv Split	25	25
EMT350S	12272	3-1/2"	Insulating Bushing wv Split	25	25
EMT400S	22001	4"	Insulating Bushing wv Split	25	25

SPLIT Insulating Bushings include cable tie



**Arlington**  
 1 Stauffer Industrial Park  
 Scranton, PA 18517  
 800/233.4717  
 Fax 570/562.0646  
 www.aifittings.com



**NEW**

Split Insulating Bushings

Scan for info



Distributed by

Patent pending  
 EMT400S/15M 0813 REV0314

**NEW!**  
more on  
reverse

# Non-Metallic Insulating Bushings for EMT

*Cable Protection at its Best*



**Easy installation on EMT!**



**EMT400S**  
4" Split Insulating Bushing  
\*Cable tie included

Arlington's non-metallic Insulating Bushings protect cable from abrasion when using EMT, Rigid, IMC or PVC rigid conduit – holding firmly in place as cable is pulled through.

When used for cable protection only these insulating bushings are a perfect substitution for costly fittings. Uses include power, computer data lines, cable TV, audio/video cables, phone, or alarm/security systems.

**Try our new, convenient SPLIT bushings. They're perfect for easy installation on EMT, and other conduit when cables are already in place.**

**SPLIT bushings are available in 2", 2-1/2", 3", 3-1/2" and 4" trade sizes. Look for the 'S' suffix in the chart on reverse.**

Arlington Insulating Bushings...

- Listed for use in environmental air handling spaces per 2014 NEC requirements 300-22(c)
- Meet 2014 NEC requirements for 300-15(c) protection
- UL/CSA Listed



Scan for info




**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
**800/233.4717**  
**Fax 570/562.0646**  
[www.aifittings.com](http://www.aifittings.com)


# Insulating Bushings for EMT, Rigid, IMC, PVC

Listed for Environmental Air Handling Spaces



**Fast, easy installation**  
 Press fit onto EMT.  
 Place board over bushing and tap onto conduit for extra-firm hold.

Arlington's Insulating Bushings meet 2014 NEC requirements for 300-15(c) protection



**EMT50**  
 1/2" Insulating Bushing  
 for EMT

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	Trade Size	DESCRIPTION Insulating Bushings	UNIT PKG	STD PKG
EMT50	12200	1/2"	Press-fit	100	1000
EMT75	12205	3/4"		100	1000
EMT100	12220	1"	Non-metallic	100	100
EMT125	12225	1-1/4"	Insulating Bushings for use with EMT	100	100
EMT150	12230	1-1/2"		100	100
EMT200	12235	2"		50	50
EMT200S	15301	2"	Insulating Bushing wv Split	50	50

**These larger EMT Bushings can also be used with rigid, IMC, PVC conduit**

EMT250	12240	2-1/2"		25	25
EMT300	12245	3"		25	25
EMT350	12250	3-1/2"		25	25
EMT400	12255	4"		25	25
EMT250S	12270	2-1/2"	Insulating Bushing wv Split	25	25
EMT300S	12271	3"	Insulating Bushing wv Split	25	25
EMT350S	12272	3-1/2"	Insulating Bushing wv Split	25	25
EMT400S	22001	4"	Insulating Bushing wv Split	25	25

SPLIT Insulating Bushings include cable tie



**Arlington**

1 Stauffer Industrial Park  
 Scranton, PA 18517  
 800/233.4717  
 Fax 570/562.0646  
 www.aifittings.com



Split Insulating Bushings

Scan for info



Distributed by

Patent pending  
 EMT400S/15M 0813 REV0314