


MORE
on
reverse

Insulating Bushings for EMT • Rigid • IMC • PVC

For Cable Protection at its Best



Arlington's non-metallic Insulating Bushings protect cable from abrasion when using EMT, Rigid, IMC or PVC rigid conduit.

They press fit onto conduit, and hold firmly in place, when cable is pulled through.

They can be substituted for costly fittings when used for cable protection only. Uses include power, computer data lines, cable TV, audio/video cables, phone/modem, or alarm/security systems.

- Fast, easy installation
- For 1/2" to 4" EMT, rigid, IMC, PVC
- Listed for use in environmental air handling spaces per 2008 NEC requirements 300-22(c)
- Meets 2008 NEC requirements for 300-15(c) protection

A  
Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Insulating Bushings for EMT • Rigid • IMC • PVC

Listed for Environmental Air Handling Spaces

Insulating Bushings for EMT



Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	Description	Unit Pkg	Std Pkg
EMT50	12200	1/2	Non-metallic insulating bushings for use with EMT	100	1000
EMT75	12205	3/4		100	1000
EMT100	12220	1		100	100
EMT125	12225	1-1/4		100	100
EMT150	12230	1-1/2		100	100
EMT200	12235	2		50	50
EMT250*	12240	2-1/2	* These bushings can also be used for rigid, IMC and PVC conduit	25	25
EMT300*	12245	3		25	25
EMT350*	12250	3-1/2		25	25
EMT400*	12255	4		25	25


Insulating Bushings for Rigid, IMC and PVC



Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	Description	Unit Pkg	Std Pkg
RGD50	51930	1/2	Non-metallic insulating bushings for use with rigid, IMC and PVC conduit	100	1000
RGD75	51932	3/4		100	1000
RGD100	51933	1		100	100
RGD125	51934	1-1/4		100	100
RGD150	51935	1-1/2		100	100
RGD200	51936	2		50	50

Fast, easy installation

Press fit onto EMT or rigid.
Then place board over bushing
and tap onto conduit for
extra-firm hold.



Distributed by

Meets 2008 NEC
requirements for
300-15(c) protection.



Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

MORE
on
reverse

Insulating Bushings for EMT • Rigid • IMC • PVC

For Cable Protection at its Best



Arlington's non-metallic Insulating Bushings protect cable from abrasion when using EMT, Rigid, IMC or PVC rigid conduit.

They press fit onto conduit, and hold firmly in place, when cable is pulled through.

They can be substituted for costly fittings when used for cable protection only. Uses include power, computer data lines, cable TV, audio/video cables, phone/modem, or alarm/security systems.

- Fast, easy installation
- For 1/2" to 4" EMT, rigid, IMC, PVC
- Listed for use in environmental air handling spaces per 2008 NEC requirements 300-22(c)
- Meets 2008 NEC requirements for 300-15(c) protection



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Insulating Bushings for EMT • Rigid • IMC • PVC

Listed for Environmental Air Handling Spaces

Insulating Bushings for EMT



Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	Description	Unit Pkg	Std Pkg
EMT50	12200	1/2	Non-metallic insulating bushings for use with EMT	100	1000
EMT75	12205	3/4		100	1000
EMT100	12220	1		100	100
EMT125	12225	1-1/4		100	100
EMT150	12230	1-1/2		100	100
EMT200	12235	2		50	50
EMT250*	12240	2-1/2	* These bushings can also be used for rigid, IMC and PVC conduit	25	25
EMT300*	12245	3		25	25
EMT350*	12250	3-1/2		25	25
EMT400*	12255	4		25	25


Insulating Bushings for Rigid, IMC and PVC



Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	Description	Unit Pkg	Std Pkg
RGD50	51930	1/2	Non-metallic insulating bushings for use with rigid, IMC and PVC conduit	100	1000
RGD75	51932	3/4		100	1000
RGD100	51933	1		100	100
RGD125	51934	1-1/4		100	100
RGD150	51935	1-1/2		100	100
RGD200	51936	2		50	50

Fast, easy installation

Press fit onto EMT or rigid.
Then place board over bushing
and tap onto conduit for
extra-firm hold.



Distributed by

Meets 2008 NEC
requirements for
300-15(c) protection.



Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com