

---

## 20" PLASTIC HINGED DOOR, ONLY (PACK OF 5)

ENP2060-5 | [On-Q](#)



---

### FEATURES & BENEFITS

The standalone hinged door attaches easily to the ENP2080-5 plastic enclosure and is reversible adding flexibility to the installation. Purchase during the project trim-out phase to complete your structured wiring installation. [Click here](#) to learn more about the unique features that will save you time and simplify installation.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Adds 1.2" of depth for cable headroom and 3rd party device compatibility.
- Extra venting along the vertical plane allows for superior heat dissipation.
- Doors stack for efficient transportation and warehousing.
- Lockable with provided screws.
- Covers drywall hole for clean finish.
- UL listed.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White (Paintable)\*

Type: Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems

UL Standard: Yes

## CONSTRUCTION INFORMATION

Material 1: ABS Plastic

## DIMENSIONS

Depth (Metric): 53.4 mm

Depth (US): 2.1"

Height (Metric): 552.9mm

Height (US): 21.77"

Width (Metric): 405.77mm

Width (US): 15.97"

Primary Packaging Weight (Metric): 4.31kg

Product Weight (Metric): 3.4 kg

Product Weight (US): 7.5 lbs

## TECHNICAL INFORMATION

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C

---

## 20" PLASTIC HINGED DOOR, ONLY (PACK OF 5)

ENP2060-5 | [On-Q](#)



---

### FEATURES & BENEFITS

The standalone hinged door attaches easily to the ENP2080-5 plastic enclosure and is reversible adding flexibility to the installation. Purchase during the project trim-out phase to complete your structured wiring installation. [Click here](#) to learn more about the unique features that will save you time and simplify installation.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Adds 1.2" of depth for cable headroom and 3rd party device compatibility.
- Extra venting along the vertical plane allows for superior heat dissipation.
- Doors stack for efficient transportation and warehousing.
- Lockable with provided screws.
- Covers drywall hole for clean finish.
- UL listed.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White (Paintable)\*

Type: Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems

UL Standard: Yes

## CONSTRUCTION INFORMATION

Material 1: ABS Plastic

## DIMENSIONS

Depth (Metric): 53.4 mm

Depth (US): 2.1"

Height (Metric): 552.9mm

Height (US): 21.77"

Width (Metric): 405.77mm

Width (US): 15.97"

Primary Packaging Weight (Metric): 4.31kg

Product Weight (Metric): 3.4 kg

Product Weight (US): 7.5 lbs

## TECHNICAL INFORMATION

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C