









Accessories

Patch Cords

| | Product Description | UPC Code | Catalog Number |
|--|--|--------------|------------------|
|  <p>ESWPT308B</p> | Two pair, CAT3 telephone patch cord. Blue | | |
| | 8 inches | 782116895267 | ESWPT308B |
| | 24 inches | 782116895274 | ESWPT324B |
| | 36 inches | 782116894390 | ESWPT336B |
| | 48 inches | 782116469239 | ESWPT348B |
|  <p>ESWPT508B</p> | Four pair, CAT5e telephone patch cord. Blue | | |
| | 8 inches | 782116895281 | ESWPT508B |
| | 24 inches | 782116895298 | ESWPT524B |
| | 36 inches | 782116894406 | ESWPT536B |
| | 48 inches | 782116469246 | ESWPT548B |
|  <p>ESWPT524O</p> | CAT5e telephone patch cord. Orange | | |
| | 24 inches | 782116469253 | ESWPT524O |
| | 36 inches | 782116469260 | ESWPT536O |
| | 48 inches | 782116469277 | ESWPT548O |
|  <p>ESWPC08</p> | RG6-rated mini digital cable. Yellow | | |
| | 8 inches | 782116895236 | ESWPC08 |
| | 24 inches | 782116895243 | ESWPC24 |
| | 36 inches | 782116895250 | ESWPC36 |
| | 48 inches | 782116469222 | ESWPC48 |

Accessories

Patch Cords

| | Product Description | UPC Code | Catalog Number |
|---|--|--------------|------------------|
|  | Two pair, CAT3 telephone patch cord. Blue | | |
| | 8 inches | 782116895267 | ESWPT308B |
| | 24 inches | 782116895274 | ESWPT324B |
| | 36 inches | 782116894390 | ESWPT336B |
| | 48 inches | 782116469239 | ESWPT348B |
|  | Four pair, CAT5e telephone patch cord. Blue | | |
| | 8 inches | 782116895281 | ESWPT508B |
| | 24 inches | 782116895298 | ESWPT524B |
| | 36 inches | 782116894406 | ESWPT536B |
| | 48 inches | 782116469246 | ESWPT548B |
|  | CAT5e telephone patch cord. Orange | | |
| | 24 inches | 782116469253 | ESWPT524O |
| | 36 inches | 782116469260 | ESWPT536O |
| | 48 inches | 782116469277 | ESWPT548O |
|  | RG6-rated mini digital cable. Yellow | | |
| | 8 inches | 782116895236 | ESWPC08 |
| | 24 inches | 782116895243 | ESWPC24 |
| | 36 inches | 782116895250 | ESWPC36 |
| | 48 inches | 782116469222 | ESWPC48 |