



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EYSX2SA 3/4" Alu Cond Seal *Crouse-Hinds*

Catalog Number	EYSX2SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Eysx Expanded Fill Sealing Fitting, Female, Copper-Free Aluminum, Vertical or Horizontal, 3/4"
Weight per unit	0.7300 (lbs/each)
Product Category	Aluminum

Features

connection	Female Threaded, Female Threaded
dimensions	1.7500 IN X 1.7500 IN X 4.3100 IN

Descriptions

Description	3/4" ALU COND SEAL
extra long description	CRS-H EYSX2 SA 3/4 AL FEM VER/HOR E
Features	EYSX expanded fill sealing fittings from Eaton Crouse-Hinds Division provide 40% wire fill capacity to allow uninterrupted runs in a conduit system. They are designed to restrict the passage of gases, vapors or flames from one portion of the electrical installation to another, limit explosions to the sealed off enclosure, and limit pre-compression or "pressure piling" in conduit systems. EYSX expanded fill sealing fittings are available for installation in both horizontal or vertical positions.
Long Description	Eaton Crouse-Hinds series EYSX expanded fill sealing fitting, Female, Copper-free aluminum, Vertical or horizontal, 3/4"
Product Type	3/4 Al Fem Ver/Hor Expand Fill Seal FT
Special Features	Horizontal/Vertical Position

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274943183
Manufacturers Part Number	EYSX2 SA
UPC	782274943183

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Expanded fill sealing fitting

Packaging

Carton	1
Package	2
Weight Per each	0.73



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	CLASS I DIV 1 2 GROUP C D, CLASS II DIV 1 2 GROUP E F G, CLASS III
standard	UL 886, CSA C22.2