



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F032841XPEC03SL 32W T8 48" Oct XP 41K 85cri

*Sylvania-Ledvance*

Catalog Number	F032841XPEC03SL
Manufacturer	Sylvania-Ledvance
Description	32W, 48" Mol, T8 Octron XP Extended Performance Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For Is or RS Operation, Ecologic, Safeline Shatter Resistant Coating to Help Contain Glass and Other Components Should The Lamp Break
Weight per unit	0.4500 (lbs/each)
Product Category	Shatter Resistant Fluorescent

### Features

amperage rating	Ballast Dependent
average life	36000
Base	Medium Bipin
Lamp Type	RAPID START
lumens	2,940
Shape	T8
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

### Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Safeline

### Dimensions and Weight

Diameter	1
Length	47.78

### Descriptions

Description	32W T8 48" OCT XP 41K 85CRI
extra long description	SYL FO32/841/XP/ECO3/SL/22278 FO328
Long Description	32W, 48" MOL, T8 OCTRON XP Extended Performance lamp, 4100K color temperature, rare earth phosphor, 85 CRI, suitable for IS or RS operation, ECOLOGIC, SAFELINE shatter resistant coating to help contain glass and other components should the lamp break
Product Type	F032841XPECO3SL 30/CS 1/Sku



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	SYLVANIA
GTIN	00046135222788
Manufacturers Part Number	FO32/841/XP/ECO3/SL/22278
UPC	046135222788

## Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

## Packaging

Carton	1
Package	30
Weight Per each	0.45

## Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------