



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F28WT5830ECO 28W T5 85 Cri 3000K Eco Fluorescent Lamp

Ge By Current Lamps

| | |
|------------------|--|
| Catalog Number | F28WT5830ECO |
| Manufacturer | Ge By Current Lamps |
| Description | Ge Ecolux®, 28 WTT, 2900 LM, 3000 KV, 85 Cri, 0.625 In Diameter, 45.2 In Length, Miniature Bi-Pin (G5) Base, 30000 HR Average Life |
| Weight per unit | 0.4000 (lbs/each) |
| Product Category | Linear Fluorescent Straight La |

Features

| | |
|--------------|-----------------------|
| average life | 30000.0 |
| Base | Miniature Bi-Pin (G5) |
| lumens | 2900.0 |
| Wattage | 28.0 |

Material, Color, and Finish

| | |
|-----------------------------|--------|
| color rendering index (cri) | 85.0 |
| color temperature | 3000.0 |

Dimensions and Weight

| | |
|----------|-------|
| Diameter | 0.625 |
| Length | 45.2 |

Descriptions

| | |
|------------------------|--|
| Description | 28W T5 85 CRI 3000K ECO FLUORESCENT LAMP |
| extra long description | GEL F28W/T5/830/ECO 46704 FLUORESC |
| Long Description | GE Ecolux®, 28 WTT, 2900 LM, 3000 KV, 85 CRI, 0.625 IN Diameter, 45.2 IN Length, Miniature Bi-Pin (G5) Base, 30000 HR Average Life |
| Product Type | 46704 Fluorescent |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168467049 |
| Manufacturers Part Number | F28W/T5/830/ECO |
| UPC | 043168467049 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | Fluorescent |
|----------------------|-------------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 40 |
| Weight Per each | 0.4 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Full Wattage