



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F48T12CW 40W T12 48" 4100K Single Pin 62 Cri Fluor

*Sylvania-Ledvance*

|                  |                                                                                                                 |
|------------------|-----------------------------------------------------------------------------------------------------------------|
| Catalog Number   | F48T12CW                                                                                                        |
| Manufacturer     | Sylvania-Ledvance                                                                                               |
| Description      | 39W, 48" Mol, T12 Instant Start Slimline Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri |
| Weight per unit  | 0.6800 (lbs/each)                                                                                               |
| Product Category | Linear Fluorescent Straight La                                                                                  |

### Features

|                           |                                     |
|---------------------------|-------------------------------------|
| amperage rating           | Ballast Dependent                   |
| average life              | 9000                                |
| Base                      | Single Pin                          |
| bulb type                 | T12                                 |
| lumens                    | 2820 Initial Lumens at 25 Degrees C |
| Shape                     | T12                                 |
| start type                | Instant Start                       |
| total harmonic distortion | Ballast Dependent                   |
| Voltage Rating            | Ballast Dependent                   |
| Wattage                   | 39                                  |

### Material, Color, and Finish

|                             |                 |
|-----------------------------|-----------------|
| color rendering index (cri) | 60              |
| color temperature           | 4200            |
| Finish                      | Phosphor Coated |

### Dimensions and Weight

|          |        |
|----------|--------|
| Diameter | 1.5 in |
|----------|--------|

### Descriptions

|                        |                                                                                                                 |
|------------------------|-----------------------------------------------------------------------------------------------------------------|
| Description            | 40W T12 48" 4100K SINGLE PIN 62 CRI FLUOR                                                                       |
| extra long description | SYL F48T12/CW/24830 F48T12CW 30/CS                                                                              |
| Long Description       | 39W, 48" MOL, T12 instant start Slimline fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI |
| Product Type           | F48T12CW 30/CS 1/Sku                                                                                            |
| Special Features       | COOL WHITE                                                                                                      |

### Manufacturer Information

|                           |                 |
|---------------------------|-----------------|
| Brand                     | SYLVANIA        |
| GTIN                      | 00046135248306  |
| Manufacturers Part Number | F48T12/CW/24830 |
| UPC                       | 046135248306    |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 30

Weight Per each ..... 0.68

## Uses, Certifications, and Standards

Application ..... Commercial/Residential