



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FB2DBCVR Dark Bronze Flor Box Cover For FB2 Floor Box

Allied Moulded

Catalog Number	FB2DBCVR
Manufacturer	Allied Moulded
Description	Floor Box Cover, Rectangular Type; Cast Brass (Cover), Closed Cell Rubber (Gasket) Material; Dark Bronze Finish; 3.5 Inch; 5.13 Inch; 1 Gang(S); UI 514C Approval; Duplex Device Type; 2.498 Inch Width X 3.5 Inch Depth X 4.312 Inch Height Box Size
Weight per unit	1.0 (lbs/each)
Product Category	Floor Boxes & Accessories

Features

Box Size	2.498 Inch Width x 3.5 Inch Depth x 4.312 Inch Height
Device Type	Duplex
Material	Cast Brass (Cover), Closed Cell Rubber (Gasket)
Number of Gangs	1

Material, Color, and Finish

Finish	Dark Bronze
--------	-------------

Dimensions and Weight

Height	5.13 Inch
Width	3.5 Inch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information

Depth 0.22 Inch; Mounting Type 2-Screw; Used On FB-2DB Floor Box; Application Floor Box Assembly for Residential Wood Floor; Applicable Standard ANSI, ISO 9001; WARNING: This product can expose you to chemicals including lead, which is known to the State

Commodity Description

FLOOR BOXES & ACCESSORIES

Description

DARK BRONZE FLOOR BOX COVER FOR FB2 FLOOR BOX

extra long description

RECTANGULAR TYPE; CAST BRASS (COVER), CLOSED CELL RUBBER (GASKET) MATERIAL; DARK BRONZE FINISH; 3.5 INCH; 5.13 INCH; 1 GANG(S); UL 514C APPROVAL; DUPLEX DEVICE TYPE; 2.498 INCH WIDTH X 3.5 INCH DEPTH X 4.312 INCH HEIGHT BOX SIZE; DEPTH 0.22 INCH; MOUNTING TYPE 2-SCREW; USED ON FB-2DB FLOOR BOX; APPLICATION FLOOR BOX ASSEMBLY FOR RESIDENTIAL WOOD FLOOR; APPLICABLE STANDARD ANSI, ISO 9001; WARNING: THIS PRODUCT CAN EXPOSE YOU TO CHEMICALS INCLUDING LEAD, WHICH IS KNOWN TO THE STATE OF CALIFORNIA TO CAUSE CAN

Long Description

FLOOR BOX COVER, RECTANGULAR TYPE; CAST BRASS (COVER), CLOSED CELL RUBBER (GASKET) MATERIAL; DARK BRONZE FINISH; 3.5 INCH; 5.13 INCH; 1 GANG(S); UL 514C APPROVAL; DUPLEX DEVICE TYPE; 2.498 INCH WIDTH X 3.5 INCH DEPTH X 4.312 INCH HEIGHT BOX SIZE

Product Type

Floor Box Cover

Manufacturer Information

Brand

Allied Moulded Products

GTIN

00085339996026

Manufacturers Part Number

FB-2DBCVR

UPC

085339996026

Taxonomies, Classifications, and Categories

Category Description

Fuses & Fuse Accessories

Type

RECTANGULAR

Packaging

Carton

1

Weight Per each

1

Uses, Certifications, and Standards

Approval

UL 514C