


**NEW!**  
**LOW COST!**

# Low-Cost, Economical Fan/Fixture Box

## with Adjustable Steel Bracket and Plastic Box



**NEW!**

**FBR423**  
Fan/fixture bracket  
between joists  
in New Construction

Captive  
fan/fixture  
bracket  
installation screws

Arlington's low cost, economical steel fan/fixture bracket with plastic box delivers super-secure, versatile on-center mounting.

Its steel bracket is fully adjustable to fit between joists spaced 16" to 24".

The box is set for on-center mounting but the 23.0 cubic inch plastic box is positionable anywhere along bracket so you can place the fan or fixture where you want it on the ceiling.

The FBR423 fan/fixture box delivers flush installation on ceilings up to 1-1/4" thick. The bracket ends are pre-set for a 1/2" ceiling. For other ceiling depths, simply bend the bracket ends along the appropriate score line engraved on the product.

- Easy mounting in new construction... fan bracket installation screws ship captive

- UL/CSA Listed

**UL rating:**

@24" on-center:  
70 lb fan; 90 lb fixture

@16" on-center:  
70 lb fan; 150 lb fixture

**CSA rating:** 50 lb fan or fixture




Bracket mounts securely to joists.



Loosen center screw to position box on bracket.



**FBR423**



Bracket ends are pre-set for a 1/2" ceiling. For other ceiling depths bend the bracket ends along the appropriate score line.

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description Fan/Fixture Box	Unit Pkg	Std Pkg
FBR423	52310	Adjustable steel bracket, 23.0 cu. in. plastic box	1	10



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517

**800/233.4717**


**Fax 570/562.0646**

**www.aifittings.com**

**NEW!**  
**LOW COST!**

# Low-Cost, Economical Fan/Fixture Box

## with Adjustable Steel Bracket and Plastic Box



**NEW!**

**FBR423**  
Fan/fixture bracket  
between joists  
in New Construction

Captive  
fan/fixture  
bracket  
installation screws

Arlington's low cost, economical steel fan/fixture bracket with plastic box delivers super-secure, versatile on-center mounting.

Its steel bracket is fully adjustable to fit between joists spaced 16" to 24".

The box is set for on-center mounting but the 23.0 cubic inch plastic box is positionable anywhere along bracket so you can place the fan or fixture where you want it on the ceiling.

The FBR423 fan/fixture box delivers flush installation on ceilings up to 1-1/4" thick. The bracket ends are pre-set for a 1/2" ceiling. For other ceiling depths, simply bend the bracket ends along the appropriate score line engraved on the product.

- Easy mounting in new construction... fan bracket installation screws ship captive

- UL/CSA Listed

**UL rating:**

@24" on-center:  
70 lb fan; 90 lb fixture

@16" on-center:  
70 lb fan; 150 lb fixture

**CSA rating:** 50 lb fan or fixture




Bracket mounts securely to joists.



Loosen center screw to position box on bracket.



**FBR423**



Bracket ends are pre-set for a 1/2" ceiling. For other ceiling depths bend the bracket ends along the appropriate score line.

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description Fan/Fixture Box	Unit Pkg	Std Pkg
FBR423	52310	Adjustable steel bracket, 23.0 cu. in. plastic box	1	10



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517

**800/233.4717**

**Fax 570/562.0646**

**www.aifittings.com**