



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FC062U SNG Sup GRP .62 CBL SNG Eye

Pass & Seymour/Legrand

Catalog Number	FC062U
Manufacturer	Pass & Seymour/Legrand
Description	FC062U: Standard Duty, Closed Mesh, Single-Eye Grip, Cable Diameter 0.62 - 0.74 Inches, Bale Length 8-In, Mesh Length 11-In, Break Strength 960 LBS.
Weight per unit	0.1200 (lbs/each)
Product Category	Cable & Cord Grips

Features

Cable Size	Cable Dia. Range: 0.620-0.740; Bale Length: 8; Mesh Length: 11
Cable Type	Various Types of Electrical Conductor/Cable
load	Approx. Break Strength: 960

Descriptions

Construction	Various Types of Pulling, Support and Strain Relief Grips
Description	SNG SUP GRP .62 CBL SNG EYE
extra long description	P&S FC062U SNG SUP GRP .62 CBL SNG
Long Description	FC062U: Standard Duty, Closed Mesh, Single-Eye Grip, Cable Diameter 0.62 - 0.74 inches, Bale Length 8-in, Mesh Length 11-in, Break Strength 960 lbs.
Product Type	SNG Sup GRP .62 CBL SNG Eye
Special Features	Standard closed mesh support grips are designed for loads up to 600 lbs. and vertical runs of no more than 100 ft. They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing. Closed mesh support grips are used when the end of the cable is accessible. Support grips are woven of corrosion-resistant tinned-bronze wire.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007980677
Manufacturers Part Number	FC062U
UPC	785007980677

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Flexcor® Support Grip Standard-Duty - Closed Mesh, Single Eye

Packaging

Carton	10
Package	150
Weight Per each	0.12



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Industrial
Capacity	Various Cable Diameter Ranges
Mounting	Consult the Factory for Mounting Recommendations
standard	UL/CSA Approval (consult factory)