



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FC40 Bus Drop SGL U Eye .4-.56 Dia

*Pass & Seymour/Legrand*

Catalog Number	FC40
Manufacturer	Pass & Seymour/Legrand
Description	FC40: Bus Drop, Closed Mesh, Single Eye, Cable Diameter 0.41 - 0.56 Inches, Bale Length 9-In, Mesh Length 5-In, Break Strength 1100 LBS.
Weight per unit	0.0900 (lbs/each)
Product Category	Cable & Cord Grips

### Features

Cable Size	Cable Dia. Range: 0.410-0.560; Bale Length: 9; Mesh Length: 5.0
Cable Type	Various Types of Electrical Conductor/Cable
load	Approx. Break Strength: 1,100

### Descriptions

Construction	Support and Strain Relief Grips, Various Types of Pulling
Description	BUS DROP SGL U EYE .4-.56 DIA
extra long description	P&S FC40 BUS DROP SNG U EYE .4-.56
Long Description	FC40: Bus Drop, Closed Mesh, Single Eye, Cable Diameter 0.41 - 0.56 inches, Bale Length 9-in, Mesh Length 5-in, Break Strength 1100 lbs.
Product Type	Bus Drop SNG U Eye .4-.56 Dia
Special Features	Bus drop grips are used as cable support. They relieve any direct tension from the critical connection and absorb vibration and flexing. Bus drop grips are woven of galvanized steel wire. They are offered with either the single eye or locking bale attachment.

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007998726
Manufacturers Part Number	FC40
UPC	785007998726

### Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Flexcor® Support Grip Bus Drop - Closed Mesh, Single Eye

### Packaging

Carton	1
Package	100
Weight Per each	0.09



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Industrial
Capacity	Various Cable Diameter Ranges
Mounting	Consult the Factory for Mounting Recommendations
standard	UL, CSA, UL/CSA Approval (consult factory)