



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FEML484LMVOLT 4' Led VPR PRF 40K 4000LM

*Lithonia Lighting - Acuity*

Catalog Number	FEML484LMVOLT
Manufacturer	Lithonia Lighting - Acuity
Description	Low-Profile Enclosed and Gasketed Industrial Led , 48" Long, Four Lamps, 120V-277V
Weight per unit	13.7 (lbs/each)
Product Category	Lighting

### Features

average life	60,000
connection	Hardwired
Fixture Type	Linear
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	4,000
Number of Lamps	4
pallet quantity	30
Shape	Rectangular
Voltage Rating	120 to 277
Warranty	1

### Material, Color, and Finish

Color	White
Lens Color	Clear
Style	Traditional

### Dimensions and Weight

Height	4.2
Length	51.75
Size	51.75x6.8x4.2 IN
Width	6.8

### Descriptions

Description	4' LED VPR PRF 40K 4000LM
extra long description	LITH FEM L48 4L MVOLT Linear
Long Description	Low-profile enclosed and gasketed industrial LED , 48" long, Four lamps, 120V-277V
Product Type	Linear



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194994110323
Manufacturers Part Number	FEM L48 4L MVOLT
UPC	194994110323

## Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	LINEAR

## Trade Size

aperture size	4FT
---------------	-----

## Packaging

Carton	1
Weight	11.2
Weight Per each	13.7

## Uses, Certifications, and Standards

Application	Automotive & Parking,Enclosed & Gasketed,Government,Manufacturing,Parking Garage,Special Applications,Sports and Recreation,Warehouses
environmental conditions	Demanding,Indoor
Mounting	Pendant,Surface,Suspended
standard	CSADLC Premium,DLC Standard