

Eaton FD3025

Catalog Number: FD3025

Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 25 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz

Photo is representative



General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	FD3025
	UPC
	786679305645
Product Length/Depth	Product Height
3.38 in	6 in
Product Width	Product Weight
4.13 in	4.35 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

25 A

Voltage rating

600 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

FD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Load side

Frame

F

Frequency rating

50/60 Hz

Interrupt rating

35 kAIC at 480 Vac

65 kAIC at 240 Vac

Number of poles

Three-pole

Resources

Application notes

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[Current limiting Series C molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Multi-wire lugs product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[StrandAble terminals product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[Breaker service centers](#)

[Counterfeit and Gray Market Awareness Guide](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[Time Current Curves for Series C® F-Frame Circuit Breakers](#)

[FD3 2D PDF](#)

[FD3 3D Inventor](#)

[F-frame Molded Case Circuit Breaker Drawing](#)

[FD3 2D Drawing Xchange](#)

[FD3 3D Model Xchange](#)

Installation instructions

[Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[F-Frame 310+ Molded-case circuit breakers 15-225A](#)

[Eaton Specification Sheet - FD3025](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C G-Frame molded case circuit breakers time current curves](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)