



GE
Lighting

94546 - GE CFL 23w T3 Spiral

FLE23HT3/2/841

GENERAL CHARACTERISTICS

| | |
|--------------------------|---------------------|
| Base Type | Screw-In |
| Life in Years | 9.1 yr |
| Rated Life Hours-nominal | 10000 h |
| Base Description | Medium Screw |
| Product Technology | Compact Fluorescent |
| Base | E26 |
| Bulb Shape | R30 |

PHOTOMETRIC CHARACTERISTICS

| | |
|--------------------------------|---------|
| Nominal Initial Lumen per Watt | 70 |
| Initial Lumens-nominal | 1600 lm |
| Color Temperature | 4100 K |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 94546 |
| Description | FLE23HT3/2/841 |
| Alternative Unit Of Measure | EACH |
| Standard Package Quantity | 10 |
| Ean UPC | 043168945462 |
| Standard Package GTIN | 00043168945462 |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 10 |
| Sales Unit | Each |
| UCC | 043168945462 |
| Alternative Unit Of Measure | CASE |

ELECTRICAL CHARACTERISTICS

| | |
|--------------------------------|---------|
| Estimated Energy Cost per Year | 2.77 \$ |
| Dimming Capability | No |
| Rated power (Watts) | 23 W |



GE
Lighting

94546 - GE CFL 23w T3 Spiral

FLE23HT3/2/841

GENERAL CHARACTERISTICS

| | |
|--------------------------|---------------------|
| Base Type | Screw-In |
| Life in Years | 9.1 yr |
| Rated Life Hours-nominal | 10000 h |
| Base Description | Medium Screw |
| Product Technology | Compact Fluorescent |
| Base | E26 |
| Bulb Shape | R30 |

PHOTOMETRIC CHARACTERISTICS

| | |
|--------------------------------|---------|
| Nominal Initial Lumen per Watt | 70 |
| Initial Lumens-nominal | 1600 lm |
| Color Temperature | 4100 K |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 94546 |
| Description | FLE23HT3/2/841 |
| Alternative Unit Of Measure | EACH |
| Standard Package Quantity | 10 |
| Ean UPC | 043168945462 |
| Standard Package GTIN | 00043168945462 |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 10 |
| Sales Unit | Each |
| UCC | 043168945462 |
| Alternative Unit Of Measure | CASE |

ELECTRICAL CHARACTERISTICS

| | |
|--------------------------------|---------|
| Estimated Energy Cost per Year | 2.77 \$ |
| Dimming Capability | No |
| Rated power (Watts) | 23 W |