



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FLED75R1AUNV8CSB 75W Led Flood 3K/4K/5K Select 10725LM BRZ 120/277V *Keystone Technologies*

Catalog Number	FLED75R1AUNV8CSB
Manufacturer	Keystone Technologies
Description	75W Led Flood Light Feat. Color Select, Rectangular Series 1 With Built In Photocell. 120-277V Input, 3000K/4000K/5000K. Standard Bronze Housing. Wide Beam Spread, Universal Mount (Slip Fitter With Trunion Mount Option Included) Dimmable
Weight per unit	7.7 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP65
lumens	10050
Nominal Length	N/A
Nominal Size	Rectangular
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	Photocell only
Wattage	75
Wire Type	N/A

Material, Color, and Finish

Base Type	N/A
color rendering index (cri)	>80 Deg
color temperature	N/A
housing color	Bronze

Descriptions

Construction	N/A
Description	75W LED FLOOD 3K/4K/5K SELECT 10725LM BRZ 120/277V
extra long description	Key KT-FLED75-R1A-UNV-8CSB-VDIM 250
Long Description	75W LED Flood Light feat. Color Select, Rectangular Series 1 with built in photocell. 120-277V Input, 3000K/4000K/5000K. Standard Bronze Housing. Wide Beam Spread, Universal Mount (Slip Fitter with Trunion Mount option included) Dimmable
Product Type	250-320W Equiv., 75W, 10725 Lumens Built In Photocell. Univr



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654130293
Manufacturers Part Number	KT-FLED75-R1A-UNV-8CSB-VDIM
UPC	843654130293

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
----------------------	---

Packaging

Carton	1
Weight Per each	7.69

Uses, Certifications, and Standards

Energy Star	N
-------------	---