



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FNQR34 Efse FNQ-R-3/4 Class CC Time Delay

Bussmann Fuses

Catalog Number	FNQR34
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Class CC Fuse, FNQ, Time-Delay, Dual-Element Current Limiting Fuse, 0.75 A, Rejection Style Fuse, Interrupting Rating Of 200KA At 600vac
Weight per unit	0.1500 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	0.75 A
class	Class CC
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
Fuse Class	Class CC
interrupt rating	200 kAIC
Material	Melamine Tube
Response Time	12 S at 200%
Voltage Rating	600 V

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	EFSE FNQ-R-3/4 CLASS CC TIME DELAY
extra long description	BUSS FNQ-R-3/4 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Long Description	Eaton Bussmann Series Class CC fuse, FNQ, time-delay, dual-element current limiting fuse, 0.75 A, rejection style fuse, interrupting rating of 200kA at 600Vac
Product Type	Class CC Time Delay
Special Features	Rejection Style



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Bussmann Fuses
Manufacturers Part Number	FNQ-R-3/4

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	FUSE

Packaging

Carton	1
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,CE Marked