



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FMLWLLNK48AL048S 4' Led Wrap Lumen & Kelvin Select 2, 000-4, 000LM

Lithonia Lighting - Acuity

Catalog Number	FMLWLLNK48AL048S
Manufacturer	Lithonia Lighting - Acuity
Description	FMLWL LNK Provides 3CCT Switchable White Technology and Adjustable Lumen Output (Alo) For Customization Of Your Space. With 3CCT Capability You Simply Adjust The Color Temperature From Warm White (3000K) to Daylight (5000K). With Alo Technology, Dial to Desired Light Output (Dim-High) to Match The Needs Of Any Job Site. The FMLWL Led Wraparound Provides Ambient Lighting For Surface-Mount Applications. The FMLWL Wrap Is Ideal For Both Residential and Commercial Use, Ideally In Kitchens, Laundry Rooms, Utili
Weight per unit	6.5 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	47.4 x 5.5 x 2.6
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	2000 LM,2900 LM,3000 LM,4000 LM,Switchable
Material	Steel
Maximum Operating Temperature	40
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120
Warranty	5
Wattage	42

Material, Color, and Finish

Color	White
color rendering index (cri)	85
color temperature	3000 ,4000 ,5000
Finish	Gloss
Style	CONTEMPORARY

Dimensions and Weight

Height	2.6
Length	47.4
Width	5.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	4' LED WRAP LUMEN & KELVIN SELECT 2,000-4,000LM
extra long description	LITH FMLWL LNK 48 ALO4 8SWW2 Wrapar
Features	Contractor Select
Long Description	FMLWL LNK provides 3CCT Switchable White Technology and Adjustable Lumen Output (ALO) for customization of your space. With 3CCT capability you simply adjust the color temperature from warm white (3000K) to daylight (5000K). With ALO technology, dial to desired light output (dim-high) to match the needs of any job site. The FMLWL LED Wraparound provides ambient lighting for surface-mount applications. The FMLWL wrap is ideal for both residential and commercial use, ideally in kitchens, laundry rooms, utili
Product Type	Wraparound

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194995061037
Manufacturers Part Number	FMLWL LNK 48 ALO4 8SWW2
UPC	194995061037

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Wraparound

Trade Size

aperture size	4FT
---------------	-----

Packaging

Carton	1
Weight	5
Weight Per each	6.5

Uses, Certifications, and Standards

Application	Government,Hospitality,Offices & Banks,Residential,Utility, Closet
environmental conditions	Indoor
Mounting	SURFACE
standard	cUL,ULENERGY STAR