

ELLIOTT ELECTRIC SUPPLY 801 Sterlington Rd. 71203-0000, LA Monroe Phone: 318-387-1621

We Deliver...Lower Cost, Quality Products, & Personal Service

Fax: 318-387-1763



FNQ12 1/2A Buss Midget Fuse Bussmann Fuses

Catalog Number	FNQ12
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNQ Fuse, Time-Delay, Motor Control Transformers, Circuits With In-Rush Currents, 0.5 A,
	Non-Indicating, Ferrule End X Ferrule End, 10 Kaic At 500 Vac,
	Nickel-Plated Bronze Endcap, Standard, 500 V
Weight per unit	0.0250 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	1/2 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	0.4100 IN X 0.4100 IN X 1.5000 IN
interrupt rating	10000 Amp (RMS Symmetrical)
Material	Nickel-plated bronze endcap
media	Yes
Voltage Rating	500 VAC

Dimensions and Weight

Size 13/32 In Diameter X 1-1/2 In Length

Descriptions Description

Description	1/2A BUSS MIDGET FUSE
extra long description	BUSS FNQ-1/2 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series FNQ fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 0.5 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V
Product Type	Buss Midget Fuse
Special Features	Nickel Plated Brass Endcap

Manufacturer Information

Brand	Eaton
GTIN	00051712786225
Manufacturers Part Number	FNQ-12
UPC	051712786225



standard

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

801 Sterlington Rd. 71203-0000, LA Monroe Phone: 318-387-1621

Fax: 318-387-1763

Taxonomies, Classifications, and Cat	egories
Category Description	MIDGET FUSES
Туре	FUSE
Availability	
Status	Inactive
Packaging	
Packaging Carton	1
Package	10
Weight Per each	0.025
Uses, Certifications, and Standards	
Application	Ind Facilities & Factories - Facility: Safety and Security Systems

RoHS Compliant, CE Marked