



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FNQR810 8/10A 600V TD Class CC Fuse

*Bussmann Fuses*

Catalog Number	FNQR810
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNO-R Fuse, 0.8 A, Class CC, Non-Indicating, Ferrule End X Ferrule End, 12 Sec At 200%, 200 Kaic, Melamine Tube, Standard, 600 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

### Features

amperage rating	0.8 A
class	Class CC
connection	Ferrule End X Ferrule End
dimensions	2.0000 IN X 0.5600 IN X 0.5600 IN
interrupt rating	200 kAIC
Material	Melamine Tube
media	Yes
Voltage Rating	600 V

### Descriptions

Description	8/10A 600V TD CLASS CC FUSE
extra long description	EFSE FNO-R-8/10 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNO-R's for your control transformer and similar control applications or
Long Description	Eaton Bussmann series FNO-R fuse, 0.8 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V
Product Type	Class CC Time Delay
Special Features	Rejection Style

### Manufacturer Information

Brand	Eaton
GTIN	00051712147026
Manufacturers Part Number	FNO-R-8/10
UPC	051712147026



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... MIDGET FUSES

Type ..... FUSE

## Packaging

Carton ..... 10

Weight Per each ..... 0.02

## Uses, Certifications, and Standards

Application ..... Ind Facilities & Factories - Facility: Safety and Security Systems

standard ..... CE Marked, RoHS Compliant