



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP14835ECO FP14835ECO Fluor Lamp

Sylvania-Ledvance

| | |
|------------------|--|
| Catalog Number | FP14835ECO |
| Manufacturer | Sylvania-Ledvance |
| Description | 14W, T5 Pentron Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic |
| Weight per unit | 0.1300 (lbs/each) |
| Product Category | Linear Fluorescent Straight La |

Features

| | |
|---------------------------|------------------------|
| amperage rating | Ballast Dependent |
| average life | 20000 |
| Base | Miniature Bipin |
| bulb type | T5 |
| lumens | 1,200 |
| Shape | T5 |
| start type | Programmed Rapid Start |
| total harmonic distortion | Ballast Dependent |
| Voltage | 230.00 V |
| Voltage Rating | Ballast Dependent |
| Wattage | 14 |

Material, Color, and Finish

| | |
|-----------------------------|-----------------|
| color rendering index (cri) | 85 |
| color temperature | 3500 |
| Finish | Phosphor Coated |

Dimensions and Weight

| | |
|----------|-------|
| Diameter | 0.625 |
|----------|-------|

Descriptions

| | |
|------------------------|--|
| Description | FP14835ECO FLUOR LAMP |
| extra long description | SYL FP14/835/ECO/20908 FP14835ECO 4 |
| Long Description | 14W, T5 PENTRON fluorescent lamp, 3500K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC |
| Product Type | FP14835ECO 40/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|--------------------|
| Brand | SYLVANIA |
| GTIN | 00046135209086 |
| Manufacturers Part Number | FP14/835/ECO/20908 |
| UPC | 046135209086 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

Packaging

Carton 1

Package 40

Weight Per each 0.13

Uses, Certifications, and Standards

Application Commercial/Residential